

XEROX.

Technology | Document Management | Consulting Services

Recommended Xerox Media for Xerox DocuColor 8000AP / 8000 / 7000

Revision:6.0 September 2007

last revision July 2007

This supersedes any previous Recommended Media for Xerox DocuColor 8000AP / 8000 / 7000 list.

Important Note:

Media recommendations made in this publication are based on qualification tests conducted using standard test images with moderate to heavy image area coverage.

Test machines are maintained within specifications defined by user documentation.

* Testing environment Temperature 23 degreesC±2, Relative Humidity 50% ±5. Relative Humidity range 20-50%.

Reliability is based on your operating environment and application mix.

Machine reliability specifications may be affected by high usage of heavy weight and specialty stocks.

In addition, variances in machine reliability may occur due to extended use of some media types.

© 2003 Xerox Corporation. All rights reserved.

Xerox®, The Document Company®, the stylized X®, and all Xerox product names and product names and product numbers mentioned in this publication are trademarks of Xerox Corporation.

Other company trademarks are also acknowledged.

Warranty disclaimer:

Xerox makes no guarantees or warranties, either expressed or implied, concerning the performance, use or replacement of non-Xerox branded media or throughput products.

Customers should inquire directly of their paper distributor or manufacturer for any guidance when purchasing a particular media product for the first time, customers are advised to purchase small quantities to insure that their expectations are met.

The quality of Xerox supplies is consistent from ream to ream and is backed by a 100% guarantee.

The quality of non-Xerox branded paper may vary from ream to ream or carton to carton, so for optimum performance on Xerox Colour equipment, use only the best - Xerox supplies.

EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 8000AP / 8000 / 7000

Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex) Business Papers (Bond, xerographic, and laser grades)	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m ²) Weight of the paper in grams per square meter	DC8000AP / 8000 / 7000 Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm	
		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4					
						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Xerox Digital Colour Impressions 80 gsm	A	3R97661	3R97662		80	OK All Trays	OK All Trays											
				3R97991	90	OK All Trays	OK All Trays											
Xerox Digital Colour Colotech + Gold 90 gsm	A		3R97990		90			OK All Trays	OK All Trays									
			3R97988		90			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech + 90 gsm	A		3R94642	3R95838	90	OK All Trays	OK All Trays											
			3R94641	3R94643	90	OK All Trays	OK All Trays											
Xerox Digital Colour Impressions 90 gsm	A		3R97664	3R97665	90	OK All Trays	OK All Trays											
			3R97663		90	OK All Trays	OK All Trays											
Xerox Digital Colour Colotech + Gold 100 gsm	A		3R97955	3R97956	100	OK All Trays	OK All Trays											
			3R97993		100	OK All Trays	OK All Trays											
Xerox Digital Colour Colotech + 100 gsm	A		3R94647	3R95839	100	OK All Trays	OK All Trays											
			3R94646	3R94648	100	OK All Trays	OK All Trays											
Xerox Digital Colour Colotech Natural White 100 gsm	A		3R97102	3R97103	100	OK All Trays	OK All Trays											
				3R97668	100	OK All Trays	OK All Trays											
Xerox Digital Colour Impressions 100 gsm	A		3R97666	3R97667	100	OK All Trays	OK All Trays											
				3R97960	120	OK All Trays	OK All Trays											
Xerox Digital Colour Colotech+ Gold 120 gsm	B		3R97959		120			OK All Trays	OK All Trays									
			3R97958		120			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech+ 120 gsm	B		3R94652	3R95840	120	OK All Trays	OK All Trays											
			3R94651	3R94653	120	OK All Trays	OK All Trays											
Xerox Digital Colour Impressions 120 gsm	A		3R97669	3R97670	120	OK All Trays	OK All Trays											
			3R9665		120	OK All Trays	OK All Trays											
Uncoated Heavy Stocks	Decurler Setting paper type																	
Xerox Digital Colour Impressions 160 gsm	A		3R98008	3R98686	160					Tray 3 & 4	Tray 3 & 4							
			3R98007	3R97965	160	OK All Trays	OK All Trays			OK All Trays	OK All Trays							
Xerox Digital Colour Colotech + Gold 160 gsm	A		3R97964		160	OK All Trays	OK All Trays			OK All Trays	OK All Trays							
			3R97963		160	OK All Trays	OK All Trays			OK All Trays	OK All Trays							
Xerox Digital Colour Colotech + 160 gsm	A		3R94657	3R95841	160	OK All Trays	OK All Trays			OK All Trays	OK All Trays							
			3R94656	3R94658	160	OK All Trays	OK All Trays			OK All Trays	OK All Trays							
Xerox Digital Colour Colotech Natural White 160 gsm	A		3R95957	3R97276	160	OK All Trays	OK All Trays			OK All Trays	OK All Trays							
			3R95956		160	OK All Trays	OK All Trays			OK All Trays	OK All Trays							
Xerox Digital Colour Colotech + Gold 200 gsm	A		3R97967	3R97968	200	OK All Trays	OK All Trays					OK All Trays	OK All Trays					
					200	OK All Trays	OK All Trays					OK All Trays	OK All Trays					
Xerox Digital Colour Colotech + 200 gsm	A		3R94662	3R95842	200	OK All Trays	OK All Trays					OK All Trays	OK All Trays					
			3R94661		200	OK All Trays	OK All Trays					OK All Trays	OK All Trays					
Xerox Digital Colour Colotech Natural White 200 gsm	A		3R95959	3R97277	200	OK All Trays	OK All Trays					OK All Trays	OK All Trays					
			3R95958		200	OK All Trays	OK All Trays					OK All Trays	OK All Trays					

EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 8000AP / 8000 / 7000

	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m2) Weight of the paper in grams per square meter	DC8000AP / 8000 / 7000 Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			
		Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex)					60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm	
						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Super Gloss Coated Heavy Stocks C1S	A	Select 106-135 gsm mode. Load with coated side up. 3R97679				135								OK All Trays	OK All Trays			
Xerox Digital Colour Colotech + SuperGloss 135 Image quality will not be as good on second side	A	Select 187-220 gsm mode. Load with coated side up. 3R97680				160								OK All Trays	OK All Trays			
Xerox Digital Colour Colotech + SuperGloss 160 Image quality will not be as good on second side	A	3R97681				160								OK All Trays	OK All Trays			
Xerox Digital Colour Colotech + SuperGloss 210 Image quality will not be as good on second side (not recommended for rated speed)		3R97683				210								OK All Trays	OK All Trays			
Xerox Digital Colour Colotech + SuperGloss 250 Image quality will not be as good on second side (not recommended for rated speed)	A	3R97682				210								OK All Trays	OK All Trays			
	A	3R97684				250										OK All Trays	Manual Duplex	
	A	3R97688				250										OK All Trays	Manual Duplex	
	A	3R97687				250										OK All Trays	Manual Duplex	
	A	3R97686				250										OK All Trays	Manual Duplex	
Specialties	Decurler Setting paper type	Various				Various												
Xerox Digital Colour Colotech Super 210 A4 Prescored White	A	3R97685 Second side image quality will not be as good as side one				160								OK All Trays	OK All Trays			
Xerox DocuCard 500 sheet box	A	3R97571 Maximum of 50 sheet stacks				160								OK All Trays	OK All Trays			
Xerox DocuGlossCard 500 sheet box	A	3R97678 Maximum of 50 sheet stacks				120								OK All Trays	OK All Trays			
Xerox ValuPeelCard Coated 500 sheet box	A	3R97953 Maximum of 50 sheet stacks				216								OK All Trays	OK All Trays			
Xerox ValuPeelCard Uncoated 500 sheet box	A	3R97952 Maximum of 50 sheet stacks				216								OK All Trays	OK All Trays			
Xerox ValuPerfCard Coated 500 sheet box	A	3R97677 Maximum of 50 sheet stacks				216								OK All Trays	OK All Trays			
Xerox ValuPerfCard Uncoated 500 sheet box	A	3R97690 Maximum of 50 sheet stacks				216								OK All Trays	OK All Trays			
Xerox Premium Never Tear	Default	3R98056 Select Coated 136-186 g/m2 Transfer ±130. Each batch run should not be more than 500 duplex. Must run 50 sheets paper between batches. Static in sheets may cause issues. 3R98058 Select Coated 136-186 g/m2 Transfer ±150. Each batch run should not be more than 500 duplex. Must run 50 sheets paper between batches. Static in sheets may cause issues. 3R98058				95 microns 120 microns								Tray 3 Only	Tray 3 Only			
Specialties	Decurler Setting paper type	Various				Various												
Xerox DuraPaper X250	A	3R97513 Select Uncoated 187-220 gsm mode. Load image side up				250 microns								OK All Trays	Manual Duplex			
Xerox DocuPac Glossy White Presentation folder	A	3R97251 Select Coated 151-220 gsm mode - load glossy side up, score line trailing				210								OK All Trays	OK All Trays			
Xerox DocuPac Matt Presentation folder	A	3R97353 Select uncoated 187-220 gsm mode- load glossy side up, score line trailing. Image quality not as good as Colotech +				180								OK All Trays	OK All Trays			
Xerox Colotech Supergloss Document Folder (not recommended for rated speed)	A	3R97634 Select coated 221-300 gsm mode for glossy side, uncoated 221-280 gsm for matt side				250										OK All Trays	Manual Duplex	
Xerox Laser Business Cards 10-UP	A	3R97512 Select uncoated 187-220 gsm mode in Tray 3- image side up.				195										Tray 3 Only	Manual Duplex	
Xerox Laser Window GraphiX Clear (window decal)	A	3R97494 Select coated 187-220 gsm mode - image side up.				125 micron								OK All Trays	OK All Trays			
Xerox Laser Window GraphiX Opaque White (window decal)	A	3R97511 Select coated 187-220 gsm mode - image side up.				125 micron								OK All Trays	OK All Trays			
	A	3R97539																
Xerox Transfer paper	A	3R97949 Select coated 136-186 gsm mode - image side up. Each batch run should not exceed 500 sheets. 100 sheets Colotech Paper should be run between batches. No more than 500 sheets per day.												OK All Trays				
Tab Stock	Decurler Setting paper type	3R97951 Feed Long Edge First, Tabs Trailing																
Xerox Digital Colour Colotech Tabs * white 100x5 reverse	B	3R97231 Select Uncoated 187-220 gsm mode. Load SEF				200								OK All Trays	OK All Trays			
Xerox Digital Colour Colotech Tabs*	B	3R97232												OK All Trays	OK All Trays			
Xerox Mylar Tabs* White 100 X 5 reverse	B	3R97229				200								OK All Trays	OK All Trays			

EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 8000AP / 8000 / 7000

	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m ²) Weight of the paper in grams per square meter	DC8000AP / 8000 / 7000 Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			
Weight Range Specification						60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm		
Instructions for Printing one side (Simplex) or two sides (Duplex)						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Transparencies (not recommended for rated speed)						FOR HIGH PRINT QUALITY Select Uncoated 221-300 gsm mode. Load transparency facing up.												
Xerox Universal Transparency with paper backing ^(50 SHEET BOX)	Default	3R98199				100 micron											OK All Trays	
Xerox Universal Transparency with paper backing SRA3	Default				3R98201	100 micron											OK All Trays	
FOR HIGH SPEED / STANDARD PRINT QUALITY Select Uncoated 187-220 gsm mode. Load transparency facing up.																		
Xerox Universal Transparency with paper backing ^(50 SHEET BOX)	Default	3R98199				100 micron											OK All Trays	
Xerox Universal Transparency with paper backing SRA3	Default				3R98201	100 micron											OK All Trays	
Label Stock						Label Stock (Approximately)												
Xerox Colour Laser Printer Labels																		
1 PER A4	C	3R93872				190											OK All Trays	
6 PER A4		3R93873				190											OK All Trays	
8 PER A4		3R93874					190										OK All Trays	
14 PER A4		3R93875					190										OK All Trays	
24 PER A4		3R97524					190										OK All Trays	
Xerox laser Colour Gloss Coated Labels																		
1 PER A4	C	3R97288				190											OK All Trays	
2 to view CD labels	C	3R97287				190											OK All Trays	
Xerox CD Colotech + Matt label & CD insert Combi Box																		
	C&A	3R97515				190 & 120											OK All Trays	
	C	3R97344				250											OK All Trays	
Xerox Durapaper Label (polyolefin face material) PER A4																		
Xerox Glossy White Self Adhesive Label A4 (not recommended for rated speed)						Select Uncoated 221-280 gsm mode. Load image side up.												
	Default	3R97245				190											OK All Trays	
Xerox Glossy White Self Adhesive Label SRA3 (not recommended for rated speed)																		
		3R97348					190											OK All Trays
Xerox Crystal Clear Adhesive Label A4 (not recommended for rated speed)																		
	Default	3R97244				190											OK All Trays	
Xerox Crystal Clear Adhesive Label SRA3 (not recommended for rated speed)																		
	Default	3R97347				190											OK All Trays	
Xerox Colobind Gloss Covers						Limit Tray capacity to 50 sheets. Image quality can vary from good to fair depending on score quality. Slightly degraded image quality on uncoated side. Image coated side 1st to minimize gloss/oil streaking. Do not image within 6mm around the score lines. Manual duplex printing only.												
Post Script custom size required for 6mm, 9mm and 12 mm splices																		
	Decurler Setting paper type	3R98022				210											OK All Trays Manual Duplex	
Spine width 1.5 mm		3R98023				210											OK All Trays Manual Duplex	
Spine width 3 mm		3R98024					210										OK All Trays Manual Duplex	
Spine width 6 mm		3R98025					210										OK All Trays Manual Duplex	
Spine width 9 mm		3R98026					210										OK All Trays Manual Duplex	
Spine width 12 mm	3R98028					210										OK All Trays Manual Duplex		
Carbonless Paper						IOT Common Software V 2.191 must be installed, and fan disabled, prior to use*												
Xerox Premium Digital Carbonless Paper						approximately												
CB Singles White																		
	A	3R99069				82											Tray 3 Only	
CB Singles White (PLE)																		
		3R99088					82											Tray 3 Only
CB Singles White (PSE)																		
		3R99089					82											Tray 3 Only
CB Singles Yellow																		
		3R99080					82											Tray 3 Only
CB Singles Pink																		
		3R99083					82											Tray 3 Only
CB Singles Blue																		
		3R99082					82											Tray 3 Only
CB Singles Green																		
		3R99081					82											Tray 3 Only
CFB Singles White																		
		3R99070					86											Tray 3 Only
CFB Singles Yellow																		
		3R99071					86											Tray 3 Only
CFB Singles Yellow (PLE)																		
		3R99091					86											Tray 3 Only
CFB Singles Yellow (PSE)																		
		3R99092					86											Tray 3 Only
CFB Singles Pink																		
		3R99074					86											Tray 3 Only
CFB Singles Pink (PLE)																		
		3R99093					86											Tray 3 Only
CFB Singles Blue																		
		3R99072					86											Tray 3 Only
CFB Singles Green																		
	3R99073					86											Tray 3 Only	
CF Singles White																		
	3R99075					82											Tray 3 Only	
CF Singles White (PLE)																		
	3R99090					82											Tray 3 Only	
CF Singles Yellow																		
	3R99076					82											Tray 3 Only	
CF Singles Pink																		
	3R99077					82											Tray 3 Only	
CF Singles Pink (PLE)																		
	3R99094					82											Tray 3 Only	
CF Singles Blue																		
	3R99078					82											Tray 3 Only	
CF Singles Green																		
	3R99079					82											Tray 3 Only	
A4+ CF Singles Yellow																		
	3R99639					82											Tray 3 Only	
A4+ CF Singles Pink																		
	3R99638					82											Tray 3 Only	
A4+ CF Singles Blue																		
	3R99644					82											Tray 3 Only	
CF Singles Tag Cream																		
	3R99146					170											Tray 3 Only	
CF Singles Tag White																		
	3R99147					170											Tray 3 Only	
A4+ CF Singles Tag Cream																		
	3R99640					170											Tray 3 Only	
A4+ CF Singles Tag Pink																		
	3R99641					170											Tray 3 Only	
2-Part White / Yellow																		
	3R99105					82/82											Tray 3 Only	
2-Part White (PLE) / Yellow																		
	3R99084		3R99133			82/82											Tray 3 Only	
2-Part White (PSE) / Yellow																		
	3R99085					82/82											Tray 3 Only	
2-Part White / Pink																		
	3R99107					82/82											Tray 3 Only	
3-Part Straight White / Yellow / Pink																		
	3R99108		3R99134			82/82											Tray 3 Only	
3-Part Straight White (PLE) / Yellow (PLE) / Pink																		
	3R99108		3R99135			82/86/82											Tray 3 Only	
3-Part Straight White (PSE) / Yellow (PSE) / Pink																		
	3R99087					82/86/82											Tray 3 Only	
3-Part Reverse Pink / Yellow / White																		
	3R99109					82/86/82											Tray 3 Only	
4-Part Straight White / Yellow / Pink / Blue																		
	3R99111					82/86/86/82											Tray 3 Only	
4-Part Reverse Blue / Pink / Yellow / White																		
	3R99112					82/86/86/82											Tray 3 Only	

* Contact your local Service Representative and refer to System Administration Guide for details